



MICAPS HPTEC3CMOS16000CA

C-mount USB 3.0 CMOS Cameras
SONY ExmorR CMOS Sensor



The HPTEC3CMOS16000CA camera utilizes a SONY ExmorR CMOS sensor for capturing images, and it connects via USB 3.0 for efficient data transfer. The camera hardware resolutions is 16MP, housed in a compact CNC aluminum alloy casing with Two-stage TE-cooling. Equipped with a two-stage peltier cooling system, the sensor chip can reach temperatures as low as -42 degrees below the ambient temperature. This feature significantly improves the signal-to-noise ratio and reduces image noise. The camera is designed with a smart structure to enhance heat radiation efficiency and prevent moisture-related issues. An controllable electric fan is incorporated to expedite the heat dissipation process.

The HPTEC3CMOS16000CA comes bundled with the advanced Micaps MicroView application for video and image processing. It supports multiple platforms, including Windows, Linux, macOS, and Android, with SDKs for various programming languages such as Native C/C++, C#/VB.NET, Python, Java, DirectShow, Twain, and more. This camera is well-suited for applications in low-light environments, as well as capturing and analyzing microscope fluorescence images. Additionally, it can be utilized for deep-sky astronomy applications.

Features

- SONY ExmorR CMOS sensor with USB 3.0 interface
- Peltier Sensor chip cooling up to 42°C below ambient temperature
- Working temperature can be regulated to specified temperature in 5 minutes
- Rolling Shutter
- IR-CUT/AR coated windows
- Up to 1 hour long time exposure
- Super-Fine™ color engine with perfect color reproduction capability Support both video and trigger modes

Applications

- Scientific research, education (teaching, demonstration and academic exchanges)
- Digital laboratory, medical research
- Industrial visual (PCB examination, IC quality control)
- Medical treatment (pathological observation)
- Food (microbial colony observation and counting)
- Aerospace, military (high sophisticated weapons)

Model No.	Sensor & Size(mm)	Pixel(μm)	G Sensitivity Dark Signal	FPS/Resolution	Binning	Exposure
HPTEC3CMOS16000CA	16M/MN34230PLJ(C) 4/3" (17.6x13.3)	3.8x3.8	2413LSB 89.1LSB (Gain = 0dB)	6@4640x3506 20@2304x1750 48.0@1536x1160 8 Bit / 12 Bit	1x1 2x2 3x3	0.1ms~1h


Other Hardware Configuration	
Spectral Range	380-650nm (with IR-filter), for Monochromatic Camera, AR Is Used
White Balance	ROI White Balance/ Manual Temp-Tint Adjustment
Color Rendering Technique	Super Fine Color Engine
Capture/Control SDK	Windows/Linux/macOS/Android Multiple Platform SDK (Native C/C++, C#/VB.NET, Python, Java, DirectShow, Twain, etc)
Recording System	Still Picture and Movie
Cooling System*	Two-stage TE-cooling System -42 °C below Camera Body Temperature

Operating Environment	
Operating Temperature	-10 °C~ 50 °C
Storage Temperature	-20 °C~ 60 °C
Operating Humidity	30~80%RH
Storage Humidity	10~60%RH
Power Supply	DC 5V over PC USB Port, External Power Adapter for Cooling System, DC12V,3A

C: Color

Software Environment

Operating System	Support Microsoft Windows XP / Vista / 7 / 8 / 10(32 & 64 bit) OS X (Mac OS X), Linux
PC Requirements	CPU: Equal to Intel Core2 2.8GHz or Higher
	Memory: 2GB or More
	USB port: USB2.0 High-speed Port
	Display: 17" or Larger
	CD-ROM



LABLINK INSTRUMENTS

- Plot no. 337, Sector 2, HSIIDC Saha, Saha, Ambala (Haryana) India - 133104.
- Plot no 3-6-164/2, 2nd Street, Hyderguda Himayatnagar, Hyderabad (Telangana)India - 500029

Contact us:

Email:- info@lablinkinstruments.com
www.lablinkinstruments.com, www.micaps.com

