



MICAPS SVTEC3CMOS45000MA

C-mount USB 3.0 CMOS Cameras
SONY PREGIUS CMOS Sensor



The SVTEC3CMOS45000MA camera is equipped with a high-quality SONY PREGIUS CMOS sensor for capturing images. It utilizes USB 3.0/GigE as the transfer interface to enhance the frame rate. SVTEC3CMOS45000MA hardware resolutions is 45MP and come with the integrated CNC aluminum alloy compact housing. Thanks to the peltier cooling sensor chip, the temperature is lowered by 5-10 degrees below the ambient level. This significantly improves the signal-to-noise ratio and reduces image noise. The camera is designed with a smart structure to ensure efficient heat radiation and prevent moisture issues. An electric fan is incorporated to speed up the heat radiation process. Working temperature can be regulated to specified temperature in 5 minutes. The SVTEC3CMOS45000MA includes an advanced video and image processing application called MicroView/MicroLite. It offers a versatile software development kit (SDK) compatible with Windows, Linux, and OSX platforms. It supports Native C/C++, C#/VB.NET, DirectShow, and Twain Control API. This camera is well-suited for applications in low-light environments, microscope fluorescence image capture and analysis, and deep-sky astronomy.

Features

- TE-cooling with controllable electric fan
- Rolling Shutter
- IR-CUT/AR coated windows
- Up to 5-minutes long time exposure
- Support capture image with video /tigger mode
- Standard C-Mount camera with Sony PREGIUS CMOS sensor
- Super-Fine color engine with perfect color reproduction capability
- With advanced video & image processing application MicroView/MicroLite

Applications

- Scientific research, education (teaching, demonstration and academic exchanges)
- Digital laboratory, medical research
- Industrial visual (PCB examination, IC quality control)
- Medical treatment (pathological observation)
- Food (microbial colony observation and counting)
- Aerospace, military (high sophisticated weapons)

Order Code	Sensor & Size(mm)	Pixel(μm)	G Sensitivity Dark Signal	FPS/Resolution	Binning	Exposure
SVTEC3CMOS45000MA	45M/IMX492(M) 4/3"(19.11x13.00)	2.315 x2.315	351mV with 1/30s 0.12mV with 1/30s	8.1@8176x5616 30.0@4080x2808 8.1@7408x5556 33.0@3696x2778 10.4@8176x4320 34.7@4096x2160 62.5@2048x1080 86.5@1360x720 8 Bit / 12 Bit	1x1(3:2) 2x2(3:2) 1x1(4:3) 2x2(4:3) 1x1(17:9) 2x2(17:9) 3x3(17:9) 4x4(17:9)	0.1ms~300s

OPERATING ENVIRONMENT

Operating Temperature	-10 °C~ 50 °C
Storage Temperature	-20 °C~ 60 °C
Operating Humidity	30~80%RH
Storage Humidity	10~60%RH
Power Supply	External Power Adapter for camera and cooling system, DC12V,3A

SOFTWARE ENVIRONMENT

Operating System	Support Microsoft Windows XP / Vista / 7 / 8 / 10(32 & 64 bit) OS X (Mac OS X), Linux
PC Requirements	CPU: Equal to Intel Core2 2.8GHz or Higher
	Memory: 2GB or More
	USB port: USB3.0 High-speed Port
	Display: 17" or Larger
	CD-ROM

OTHER HARDWARE CONFIGURATION

Spectral Range	380-650nm (with IR-filter), for Monochromatic Camera, AR Is Used
White Balance	ROI White Balance/ Manual Temp-Tint Adjustment
Color Rendering Technique	Super Fine Color Engine
Capture/Control SDK	Windows/Linux/macOS/Android Multiple Platform SDK(Native C/C++, C#/VB.NET, Python, Java, DirectShow, Twain, etc);
Recording System	Still Picture and Movie
Cooling System*	Two-stage TE-cooling System -42 °C below Camera Body Temperature

M:Monochrome, GS: Rolling Shutter

LABLINK INSTRUMENTS

- Plot no. 337, Sector 2, HSIIDC Saha, Saha, Ambala (Haryana) India - 133104.
- Plot no 3-6-164/2, 2nd Street, Hyderguda Himayatnagar, Hyderabad (Telangana)India - 500029

Contact us:

Email:- info@lablinkinstruments.com
www.lablinkinstruments.com, www.micaps.com

