

MICAPS WFTINYCMOS5100CB

CMOS eyepiece Cameras USB 2.0



The Micaps WFTINYCMOS5100CB is an upgraded version of Micaps' compact CMOS eyepiece camera, featuring a fixed reduction lens that expands the field of view when used with a microscope eyepiece tube. Designed to be both simple and efficient, the "WFTINYCMOS" name reflects its lightweight, compact build ("WF" for wide field, "TINY" for its size, and "CMOS" for the sensor type). It offers an economical solution without compromising on functionality. Equipped with a high-speed USB 2.0 interface, the WFTINYCMOS ensures smooth, uninterrupted video streaming at high frame rates. It also comes with the powerful MicroView software, which provides advanced image and video processing tools for enhanced usability. This camera is a great way to convert standard mono or binocular student microscopes into digital microscopes. And with the included 23.2 mm to 30 mm or 23.2 mm to 30.75 mm adapter rings, it's also compatible with stereo microscopes, making it easy to upgrade them into digital stereo microscopes.

Features

- Microscope eyepiece Camera with 23.2 diameter and compact size
- An extension of Micaps TINYCMOS Camera with fixed reduction lens to ensure the full field of view of the microscope from the eyepiece can be imaged to the CMOS sensor
- High-quality Camera with Aptina CMOS sensor
- Auto white balance and auto-exposure; Brightness, contrast, chroma, and saturation can be adjusted
- High-speed USB2.0 interface and high frame rate video display keep the screen smooth without interruption
- With advanced video & image processing application MicroView

Applications

- Scientific research, education (teaching, demonstration and academic exchanges)
- Digital laboratory, medical research
- Industrial visual (PCB examination, IC quality control)
- Medical treatment (pathological observation)
- Food (microbial colony observation and counting)
- Aerospace, military (high sophisticated weapons)

Order Code	Sensor & Size(mm)	Pixel(μm)	G Sensitivity Dark Signal	FPS/Resolution	Binning	Exposure
WFTINYCMOS05100CB	5.1M/IMX335(C) 1/2.8" (5.18x3.89)	2.0x2.0	505mV 70dB 43dB	26@2592x1944 26@1280x960 26@640x480	1x1 1x1 1x1	0.1-2000 ms

Software Environment Under Lan/wan/usb Video Output

Spectral Range	380-650nm (with IR-cut Filter)
White Balance	Auto/ROI/Manual White Balance
Color Technique	Super Fine Color Engine
Capture/Control SDK	Windows/Linux/macOS/Android Multiple Platform SDK(Native C/C++, C#/VB.NET, Python, Java, DirectShow, Twain, etc);
Recording System	Still Picture and Movie
Data Format	MJPEG
Cooling System*	Natural
Operating System	Microsoft® Windows® XP / Vista / 7 / 8 / 8.1 / 10(32 & 64 bit), OSx(Mac OS X), LINUX
PC Requirements	CPU: Equal to Intel Core2 2.8GHz or Higher, Memory: 4GB or More, Ethernet Port: RJ45 Ethernet Port, Display:19" or Larger, CD-ROM

Operating Environment

Operating Temperature (in Centidegree)	-10°~50°
Storage Temperature (in Centidegree)	-20°~60°
Operating Humidity	30~80%RH
Storage Humidity	10~60%RH
Power Supply	DC 5V over PC USB port

LABLINK INSTRUMENTS

- Plot no. 337, Sector 2, HSIIDC Saha, Saha, Ambala (Haryana) India - 133104.
- Plot no 3-6-164/2, 2nd Street, Hyderguda Himayatnagar, Hyderabad (Telangana)India - 500029

Contact us:

Email:- info@lablinkinstruments.com
www.lablinkinstruments.com, www.micaps.com